



Printed Board Layout
Component side

1) Einlötlötstifte passend für Lochungen
 ø1 ±0.1 nach IEC 60326-3
 Solder pins for PCB connections
 ø1 ±0.1 as per IEC 60326-3
 À souder pour des trous de ø1 ±0.1
 selon IEC 60326-3

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maße/ Free size tolerances	
Part No.	Performance level	Reference	Mod.	Dat.	Name	Detail.	Dat.	Name	Maßstab/ Scale 1,5:1	SEK 18 Male Connector Standard 14 poles Angled pins Long locking levers
09185147901	3	4,5								
09185146901	2	4,5								
09185145901	0,76 µm Au	4,5								
09185147903	3	2,9	29753	11-MAR-02	JB	Insp.	03-DEC-01	JMV		
09185146903	2	2,9	29739	03-DEC-01	JB	Stand.				
09185145903	0,76 µm Au	2,9	27931	15-JUNE-00	JB					
Bestell-Nr. Part-No. Reference	Anforderungsstufe performance level Niveau de qualite	α	26554	01-DEC-99	JB					
			HARTING EURL F-95972 Paris					TB 0918514x90x Sub.		Blatt/ page 2/2