





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	02/28/18	JLABOY




P2
SHIELDED RJ45 MODULAR PLUG
GOLD PLATED CONTACTS
(8P8C)

P1
SHIELDED RJ45 MODULAR PLUG
GOLD PLATED CONTACTS
(8P8C)



HIGH FLEX, CAT5e CABLE
CONDUCTOR: FOUR TWISTED PAIR, 26AWG STRANDED TINNED COPPER
SHIELD: TINNED COPPER BRAIDED
CABLE JACKET: PU, DARK BLUE, NOM DIA .228[5.80]
OPERATING TEMPERATURE RANGE: -20°C TO +80°C



PART NUMBER	LENGTH	
	FEET	METERS
TRD855SRA7DBL-05M	1.64	0.5
TRD855SRA7DBL-1M	3.28	1.0
TRD855SRA7DBL-2M	6.56	2.0
TRD855SRA7DBL-3M	9.84	3.0
TRD855SRA7DBL-4M	13.12	4.0
TRD855SRA7DBL-5M	16.41	5.0
TRD855SRA7DBL-10M	32.82	10.0

- NOTES:**
1. PLUG CONFORMS TO TIA-1096
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	APPROVALS D.CUI CHECKED BY W.LI APPROVED BY S.PAN	DATE 02/03/18 02/03/18 02/03/18	50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR
	PROJECTION 			PRODUCT DESCRIPTION C5e RJ45 S/UTP STR-RGT 26STR PUR HIFLX DBLU
	COLOR VARIATIONS MAY OCCUR	SIZE A		FSCM NO. 43321
SCALE: NONE		CAD FILE: TRD855SRA7DBL.SLDRW	REV. A	