


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/23/18	D.FRISIELLO



2X RJ45 (8P8C) SHIELDED PLUG

MODEL NUMBER	LENGTH FEET [METERS]
TRA6261-1F	1.0 [.30]
TRA6261-2F	2.0 [.61]
TRA6261-3F	3.0 [.91]
TRA6261-5F	5.0 [1.52]
TRA6261-10F	10.0 [3.05]
TRA6261-15F	15.0 [4.57]
TRA6261-25F	25.0 [7.62]
TRA6261-50F	50.0 [15.24]
TRA6261-75F	75.0 [22.86]
TRA6261-100F	100.0 [30.48]
TRA6261-125F	125.0 [38.10]
TRA6261-150F	150.0 [45.72]

4TP, CAT 6a, 26AWG STRANDED SILVER PLATED COPPER WITH ALUM/POLY FOIL SHIELD AND ROUND TINNED PLATED COPPER BRAID, (85% MIN. COVERAGE). JACKET: FEP, BLUE  
 OPERATING TEMPERATURE RANGE: -55 °C TO +150 °C  
 NOM. DIA: .230" [5.84], MIN. BEND RAD: 1.15" [29.2]



**NOTES:**

- FIRE PROPERTIES: (FST)  
 MEETS OR EXCEEDS THE APPLICABLE REQUIREMENTS OF FAR 25.869, FAR 25.853, ABD0031, AND D6-51377.
- LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
  - PLUG CONFORMS TO TIA-1096.
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	2/22/18	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ± .005 [1.3]	CHECKED BY D.GUITADAURO	2/23/18	CATEGORY <b>TELECOM/MODULAR</b>
	APPROVED BY D.GUITADAURO	2/23/18	
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION <b>C6a SF/UTP 26STR FEP BLU +150°C</b>	
	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
		DWG. NO. <b>TRA6261</b>	REV. <b>A</b>
		SCALE: NONE	CAD FILE: TRA6261.SLDDRW SHEET 1 OF 1