



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	02/28/2018	DCUI
B	ECN 9429: ADD 6 METER LENGTH TO CHART	09/19/2018	DFRISIELLO



HIGH FLEX, CAT5e CABLE
 CONDUCTOR: FOUR TWISTED PAIR, 26AWG STRANDED TINNED COPPER
 SHIELD: TINNED COPPER BRAIDED
 CABLE JACKET: PU, DARK BLUE, NOM DIA .228[5.80]
 OPERATING TEMPERATURE RANGE: -20°C TO +80°C



MODEL NUMBER	LENGTH	
	METERS	FEET
TRG515-P6D-1M	1.0	3.28
TRG515-P6D-2M	2.0	6.56
TRG515-P6D-3M	3.0	9.84
TRG515-P6D-4M	4.0	13.12
TRG515-P6D-5M	5.0	16.41
TRG515-P6D-6M	6.0	19.69
TRG515-P6D-10M	10.0	32.82

- NOTES:**
1. PLUG CONFORMS TO TIA-1096
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:**
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY: CN_Derek_Cui CHECKED BY: W.LI APPROVED BY: CN_Shawn_Pan	02/03/2018		02/03/2018	CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.27]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION C5e RJ45/GigE S/UTP 26STR PUR HIFLX DBLU		
PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TRG515-P6D	REV. B
		SCALE: NONE	CAD FILE: TRG515-P6D.SLDDRW		SHEET 1 OF 1