



NOTES:

1. MATERIAL: POLYBUTYLENE TEREPHTHALATE (PBT), COLOUR NATURAL.
2. UL FLAMMABILITY RATING: UL 94 V-0
3. PART IS DESIGNED TO BE USED IN 85084 SERIES RECEPTACLE ASSEMBLIES AND 85083/93792 SERIES BLADE ASSEMBLIES.
4. CAVITY NUMBER IN THIS LOCATION 2mm HIGH, RAISED 0.1mm MAX.
5. APPLICATION SPECIFICATION: 850830010 PSA.
6. MOQ 5000 PIECES. PARTS TO BE BULK PACKED IN BAGS OF 1000 PIECES WITH 5 BAGS IN A BOX. SEE 937320001 PSK.

LAST INSPECTION NUMBER USED: 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
QUALITY SYMBOLS	ORIGINAL RELEASE	EC NO: 102173	DRWN: BODEA	CHK'D: JDWALLACE	APPR: JDWALLACE	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	molex			
						4 PLACES ±	ANGULAR TOL ± °	mm	5:1				
▽A = 0						3 PLACES ±		DRWN BY	DATE	SRC POWER BLIND CAVITY PLUG			
▽E = 0						2 PLACES ± 0.3		BODEA	2015/12/14				
▽B = 0						1 PLACE ± 0.5		CHK'D BY	DATE	PRODUCT CUSTOMER DRAWING			
▼ = 0						0 PLACES ±		SMCGREEVY					
▽C = 0						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		APPR BY	DATE	SERIES: 93732 MATERIAL NUMBER: 937320001 CUSTOMER: GENERAL MARKET			
⊠ = 0						DRAWING SIZE	THIRD ANGLE PROJECTION	JDWALLACE	2016/01/08				
■ = 0						A3		DOCUMENT NUMBER: 937320001			DOC TYPE: PSD	DOC PART: 000	SHEET NUMBER: 1 OF 1
▽ = 0													