


CABLE VIEW



Length table		Color
1	0.5M	White
2	1M	
3	1.8M	
4	3M	Black
5	5M	

WIRING			
P1			P2
PIN 1	Red		PIN 1
PIN 2	Green		PIN 2
PIN 3	White		PIN 3
			PIN 4
PIN 4	Black		PIN 5
Shell	Braid		Shell

5	OVER MOLDING	PVC	2	PC	
4	INNER MOLDING	PE NATURE COLOR	2	PC	
3	USB B /PLUG	NICKEL PLATING	1	PC	
2	USB A /PLUG	NICKEL PLATING	1	PC	
1	RAW CABLE	(7/0.12BC)x2P+(7/0.12BC)x2C+D(1/0.25BC)+AL-Foil+48/0.10AL-Mg+PVC, OD:4.0mm	L+0.1	M	
NO	PART NAME	SPECIFICATION	Q'TY	UNIT	PART NO

单位: mm	公差要求	PRO-SIGNAL			
	零件图号 NO.				
尺寸		图纸编号 NO.			
Designed by		数量	比例	页数	版本
Checked by		1	1:1	1/1	A
Approved by					