


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	DESCRIPTION
A	Initial Release



- Note:
- * IP: IP67.
 - * Housing: Thermoplastic, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * O-Ring: Silicone, Grey.
 - * Clamp Ring: Zinc Alloy, Nickel Plated.
 - * Sealing Nut: Zinc Alloy, Nickel Plated.
 - * Seal For Cable OD: $\varnothing 4.0\text{mm} \sim \varnothing 7.5\text{mm}$
 - * Applicable Wire gauge (Stranded wire cross section) 20AWG-24AWG
 - * Mating Recommended tightening torque: 3-4 kgf.cm / 0.29-0.39 N.m
 - * Sealing-Nut Recommended tightening torque: 4-6 kgf.cm / 0.39-0.59 N.m
 - * Detailed applicable wire specifications may vary depending on the actual wire construction.

A	UNIT:mm		TITLE		ITEM NO	DRAWN BY	DATE
	TOLERANCE	± 0.5	M12 Shielded Ass'y 4PIN M Conn. M Pin		MSDS-04BMMC-SR7001	Xiaofeng	2019/08/09
	SCALE	Free	SIZE	A4	SHEET	1	OF
	REV.	A	WC-REV.	.0	((C)) Inspection item		DATE
					CUSTOMER	APPROVED BY	DATE
					ALTW	Jerry	2019/08/09

Amphenol LTW
安費諾亮泰企業股份有限公司