



MATERIAL NO.	ENGINEERING NO.	LENGTH "L"	LENGTH "A"	LENGTH "B"	LENGTH "C"	POWER-UP	LINE PLUG	LOAD CONNECTORS
1301530279	20052-Y-20MH	22 FT & 6 IN	20FT	6 IN	6 IN	MANUAL	N/A	15W33
1301530283	20052-Y-30MH	32 FT & 6 IN	30FT	6 IN	6 IN	MANUAL	N/A	15W33
1301530284	20052-Y-45MH	47 FT & 6 IN	45FT	6 IN	6 IN	MANUAL	N/A	15W33
1301530285	20052-Y-60MH	62 FT & 6 IN	60FT	6 IN	6 IN	MANUAL	N/A	15W33
1301530286	20052-Y-2MH	4 FT & 6 IN	2FT	6 IN	6 IN	MANUAL	N/A	15W33

TECHNICAL:

RATED VOLTAGE: 120 VAC
 OPERATING VOLTAGE RANGE: 85% TO 110% RATED
 CURRENT: UP TO 20 AMPS
 FREQUENCY: 60 Hz
 TRIP LEVEL: 5mA ± 1mA
 PHASE: SINGLE
 RESPONSE TIME: 25mS MAX
 AGENCY APPROVAL: NONE

ADD PART 1301530286 EC NO.: IFCG2019-0311 DRWN: BPATTERS 12/21/18 CHKD: HKNEELAN 2018/06/20 APPR: HKNEELAN 2018/08/21	QUALITY SYMBOL	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
	▽=0 ∇=0	mm INCH	INCH	NTS	INCH	
		4 PLACES ±--- ±---	DRAWN BY DATE	TITLE		
		3 PLACES ±--- ±.005	HRUIZ01 2013/02/11	INLINE GFCI MANUAL RESET #12-3 CORD & Y-SPLICE 20A 125VAC 60HZ 2400W		
	2 PLACES ±--- ±.010	CHECKED BY DATE	MOLEX INCORPORATED			
	1 PLACE ±--- ±.020	APPROVED BY DATE	MATERIAL NO. SEE TABLE			
		HKNEELAN 2018/08/21	DOCUMENT NO. SD-130153-0279			
			SHEET NO. 1 OF 1			
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			