



A RIPLEY® BRAND

# MC02-7000 25mm Duct Cutter

Part # MC02-7000

## Instruction Sheet

Page 1 of 1

**WARNING: THIS TOOL SHOULD NOT BE USED ON LIVE ELECTRICAL CIRCUITS. IT IS NOT PROTECTED AGAINST ELECTRICAL SHOCK!**  
ALWAYS USE OSHA/ANSI/CE OR OTHER INDUSTRY APPROVED EYE PROTECTION WHEN USING TOOLS. THIS TOOL IS NOT TO BE USED FOR PURPOSES OTHER THAN INTENDED. READ CAREFULLY AND UNDERSTAND INSTRUCTIONS BEFORE USING THIS TOOL.




The *Miller*® **MC02-7000** Duct Cutter is designed to make clean, square, and burr-free ring cuts in plastic fiber ducts up to 25 mm diameter. This duct cutter is ideal for cutting or scoring PVC, CPVC, HDPE, and other plastic tubing while protecting the inside fibers.

### Features and Specifications

- Duct size range: 0-25mm diameter
- Indexing guide base to match duct size
- Safety lock to close tool
- Blade material: SK5 steel, heat treated and nickel plated
- Body material: ABS
- Length: 8.5" / 216mm
- Weight 206g

### Operation

- The MC02-7000 is built with a rotating guide base with three size forms. Use the release button (A) and index to the diameter range as required: small (0-8mm), medium (9-18mm) large (19-25mm).
- Close the handles and rotate the tool to score or cut through the duct as desired.



**WARRANTY: RIPLEY warrants its products against defective materials and workmanship for a period of one year from date of shipment from the RIPLEY factory provided the product is utilized in accordance with instructions and specified ratings.**



Ripley Tools LLC  
46 Nooks Hill Road, Cromwell, CT 06416

P: +1 (800) 528-8665  
F: +1 (860) 635-3631

csr@ripley-tools.com  
www.ripley-tools.com

Doc. No. MC02-6000  
Approval: 08-06-20