


REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	A	ECN 0553	20-MAY-05	
	B	ECN 0601	10-AUG-06	

NO LOGO






NORTECH LOGO





PART NUMBER INFORMATION

PART#	LOGO STYLE	SUPPLIED
A30E300000	NO LOGO	BULK
C88E300000	NO LOGO	PACKAGED
A30E301000	NORTECH LOGO	BULK
C88E301000	NORTECH LOGO	PACKAGED



 #4-40 X 7/16" FILLISTER HEAD MACHINE SCREW  
 MATERIAL - STEEL  
 FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)  
 QTY: 2 EACH

 #4-40 #2 BLANK HEX NUT  
 MATERIAL - STEEL  
 FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)  
 QTY: 2 EACH

 #4-40 X 1/2" FILLISTER HEAD CAPTIVE SCREW  
 MATERIAL - STEEL  
 FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)  
 QTY: 2 EACH

 #4 SADDLE WASHER  
 MATERIAL - STEEL  
 FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)  
 QTY: 2 EACH

CONNECTOR COVER:

- 1.MATERIAL: ABS COMPOUND - UL94HB
- 2.FINISH: NICKEL PLATING PER NTC SPECIFICATION N/T 000500
- 3.DIMENSIONS: INCHES [MM]
- 4.TOLERANCE: ±0.015 [0.381]

COMPRESSION INSERT TREE

- 1.MATERIAL: THERMOPLASTIC
- 2.COLOR: BLACK
- 3.DUROMETER: 75 ±5 TYPE A PER ASTM D2240
- 4.DIMENSIONS: INCHES [MM]
- 5.TOLERANCE: ±0.020 [0.508]

THIS IS A CONTROLLED DOCUMENT AND IS SUBJECT TO CHANGE. CONTACT NORTHERN TECHNOLOGIES ENGINEERING FOR THE LATEST REVISION.

UNLESS OTHERWISE SPECIFIED  
 1. ALL DIMENSIONS ARE IN INCHES (MM)  
 2. DIMENSIONS ARE TYPICAL

**Northern Technologies**

THIS DRAWING IS THE PROPERTY OF NORTHERN TECHNOLOGIES AND SHOULD NOT BE REPRODUCED WITHOUT NORTHERN TECHNOLOGIES WRITTEN PERMISSION.

DRAWN JSD		10-FEB-05		PART NUMBER SEE PART NUMBER INFORMATION	
CHECKED SCN		10-FEB-05		DESCRIPTION CMP 09 STR EXIT TWO PIECE METALIZED PLASTIC COVER	
ISSUED		10-FEB-05		SIZE B	CODE 200_131
				DWG NO. 0002-200-131	REV
				SCALE 1:1	SHEET 1 OF 1