



Revision	Date	Note
01	2007/11/23	Module Assy



- Specification**
1. Display: OLED (Yellow)
 2. Dot Matrix: 128x64
 3. Dot Size: 0.45x0.45mm
 4. Dot Pitch: 0.48x0.48mm
 5. Aperture Rate: 88%
 6. Active Area: 61.41x30.69mm
 7. IC: SSD1305T7

Pin Assignment	
NO.	SYMBOL
1	VCC
2	VCOMH
3	IREF
4	D7
5	D6
6	D5
7	D4
8	D3
9	D2
10	D1
11	D0
12	E/RD#
13	R/W#
14	D/C#
15	RES#
16	CS#
17	BS2
18	BS1
19	VDD
20	NC
21	VSS
22	VSS



General Tolerance		CONFIDENTIAL		Scale	Unit	Sheet	PROJECT CODE	
Length (mm)	Tolerance(mm)			1:1	mm	1/1	PMO19301	
0 ~ 8	±0.1			Module	Spec.	Approved	PART NAME	REVISION
8 ~ 25	±0.2						Module Assy	01
25 ~ 50	±0.3	David Li	Kevan Huang	David Li	HC Lin	Strong Tsai	PARTS NO.	REVISION