

# HUBER+SUHNER® DATA SHEET


## Coaxial Cable Connector: 16\_MCX-50-2-104/111\_N\_-1 Rev.: A



### Description

Right angle cable plug for semi-rigid cable

Interface standards  
IEC 60169-36\_CECC 22220



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 6 GHz

#### Mechanical Data

Centre contact soldered  
Outer contact soldered  
Weight 0.0008 kg

#### Environmental Data

Operating Temperature -65 °C to 165 °C

#### Material Data

##### Piece Parts

Centre contact	Brass
Outer contact	Copper Beryllium Alloy
Body	Brass
Insulator	PFA / PTFE

##### Surface Plating

Gold Plating (Nickel underplated)  
SUCOPRO Plating  
SUCOPRO Plating

#### Related Documents

Outline drawing	DOU-00006447
Catalogue drawing	DOU-00006449
Assembly instruction	DOC-0000180001

#### Ordering Information

Bulk 100 pcs package 16\_MCX-50-2-104/111\_NH-1

#### Additional Information

Suitable cable EZ\_86\_TP\_M17

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**