

GDR 10,8-LI Professional




Cordless impact wrench

GDR 10,8-LI Professional

The shortest cordless impact driver in its class.

- At 137 mm it has the shortest design in the 10.8 Volt class for optimum handling, especially when driving screws overhead and in tight spaces
- Powerful 105 Nm torque for 80% of all conventional cordless impact driver applications in metal and concrete
- High speed (2,600 rpm) for fast work progress.



- Unique Bosch Premium lithium-ion technology for 400% longer lifetime and unbeatable battery runtime
- Bosch Electronic Cell Protection (ECP): protects the battery against overload, overheating and total discharge
- Integrated LED light for illuminating the work area, even in dark places

Part no. 0 601 9A6 901

- L-BOXX inlay (2 608 438 014)
- Box

Part no. 0 601 9A6 970

- 2 x 1.3 Ah Li-Ion batteries (2 607 336 014)
- Quick Charger AL 1130 CV (2 607 225 136)

Part no. 0 601 9A6 971

- L-BOXX (2 608 438 691)
- 2 x 1.3 Ah Li-Ion batteries (2 607 336 014)
- Quick Charger AL 1130 CV (2 607 225 136)

Technical data

13/01/2011

GDR 10,8-LI Professional - Cordless i...

No-load speed	0 – 2.600 rpm
Weight incl. battery	1,0 kg
Torque, max. (hard screwdriving applications)	105 Nm
Rated impact rate	0 – 3.100 bpm
Battery voltage	10,8 V
Toolholder	1/4" internal hexagon
Screw diameter	
Screw diameter	M4-M12

Functions

- Forward/reverse operation
- Electronic
- Softgrip