

# SONY

**DAV-DZ330**

Easy to use DVD home cinema system with music/movie playback via USB



## Specifications

### Amplifier

Power Output - Total (RMS 10%)	1000W
Power Output - Center (RMS)	167W
Power Output - Front (RMS)	167W x2
Power Output - Sub-woofer (RMS)	165W
Power Output - Surround (RMS)	167W x 2
S-Master	YES

### DVD / SACD / VCD / CD Player & Recorder

CD-R / CD-RW Playback	YES / YES
D / A Converter (Video)	108MHz / 12bit
DivX®	NO
DVD / CD / SACD TEXT	YES / YES / YES
DVD / DVD Audio / SACD / CD / Video CD	YES / - / YES / YES / YES
DVD-R / +R / +R DL / +RW / -RW / -RW (VR) Playback (* Some discs may not be played back)	YES / YES / YES / YES / YES / YES
DVD-RW (CPRM) Playback	NO
JPEG Playback	YES
mp3 Playback	YES
mp3 / ID3Tag Ver.1.1 / ID3Tag Ver.2.0	YES / YES / YES
Mechanism Tray Lock	YES
Mechanism Type	1 disc tray
OSD control	YES
Picture Navigator	NO
Shuffle: DVD / CD / VCD / SACD	- / YES / YES / YES
Program: DVD / CD / VCD / SACD	- / YES / YES / -
Repeat: DVD / CD / VCD / SACD	YES / YES / YES / YES
Precision Cinema Progressive	NO
Progressive Scan (NTSC / PAL)	NO
VCD Version 2.0	YES

### Equalizer

Portable Audio Enhancer	YES
Night Mode	NO
Dynamic bass boost	NO

<b>Function</b>	
DVD	YES
TUNER (FM, AM)	FM
DIGITAL MEDIA PORT	NO
USB	YES
Audio In	NO
SAT	NO
TV	YES

<b>Input / Output</b>	
Audio Line IN (Analog)	NO
Audio Line IN (Optical)	NO
Audio Line IN (Coaxial)	NO
Audio Input (Front, mini)	NO
D.C.A.C. (Auto Calibration)	YES
SCART (TV audio in)	NO
SCART (COMPOSITE-out / RGB-out / AUDIO-in)	1
Speaker Terminal (Front / Center / Surround / Subwoofer)	YES / YES / - / YES
Video Signal OUT (Component)	NO
Video Signal OUT (HDMI™) Upscale720p / 1080i for DVD	1 (1080p upscale)
DIGITAL MEDIA PORT	NO
iPod® / iPhone dock	NO

<b>Others</b>	
DEMO Mode	YES
Dimmer	YES
Timer (REC / PLAY / SLEEP)	YES
VACS	YES
BRAVIA sync	YES

<b>Power adjustment</b>	
Power Consumption	170W
Power Consumption at stand by	less than 0.25W
Power Save Mode	YES
Power Requirement	220V-240V AC, 50 / 60Hz

<b>Surround / Effects</b>	
A / V SYNC (Lip Sync)	YES
DTS	YES
Dolby® Digital	YES
Dolby® ProLogic / Prologic I / Prologic II	- / - / YES
Movie / Music Mode	YES

<b>Tuner</b>	
Band	FM
External FM / AM Antenna	YES (75ohm) / -
RDS ( PS / PTY / EON)	- / - / -
Station Preset	FM20
Tuning Range (FM)	87.5 MHz-108.0 MHz (50 kHzstep)

<b>Guarantee</b>	
Guarantee in Months	-