



Acclaim series - 'Flat' short scale meters

Moving coil



- Flat "no barrel" design
- Slide in scale plates
- Modular for front or rear of panel mounting
- Optional cover and picture frame bezel
- Ex-stock for immediate delivery



Meter without cover for window mount (Not to scale)



Optional "picture frame" mounting bezel (Not to scale)

ACCLAIM 'FLAT' PROFILE METERS

Attractive slim style 'flat' meters incorporating an ultra thin sandwich type movement. Normal surface mounting using the two insulated input terminals, saves space behind the panel and eliminates the need for complex barrel cut-outs. Can also replace conventional barrel meters using the four corner screw fixings provided. Alternatively, the Acclaim range can be rear mounted via a simple window cut out in the panel or using the optional picture frame bezel.


Application: For instrument panels, hand held equipment, process control and test equipment.

Construction: The meters are housed in a black plastic case assembly with clear acrylic front. The optional black cover or picture frame bezel, clips over the front of the meter concealing all but the viewing window. To avoiding damage to the pointer or movement, a rear compartment between the terminals is accessible for fitting ranging components and the scale can slide in from the side, eliminating the need to open the meter.

Movements: The meters are supplied with unique ultra thin sandwich type movements. They are of robust taut band moving coil construction giving excellent shock and vibration resistance. They have a linear scale shape and flattened arc.

Dimensions

	Window		Cover										Cut outs	
	A	B	A	B	C	D	E	F	G	H	Win	Bez		
AM25	78	60	81.5	63.5	48	48	50	36	71.5 x 27.5	81.2 x 36.2	81.5 x 36.5	79.5 x 33.45		
AM35	95.5	75	99.5	78.5	57	57	50	41	89.5 x 39.5	99.2 x 49.2	99.5 x 49.5	97.4 x 46.4		
AM45	132	102	135.5	105.5	100	90	50	56	126 x 59	135.2 x 68.2	135.5 x 68.5	133.4 x 65.2		



To surface mount, drill 2 x 8mm holes for terminals (and fixing) with centres at dimension E, F and 4 x 3.5mm holes with centres at dimensions C, D (optional).

Specifications

	AM25	AM35	AM45
Scale length:	45	65	95
Accuracy:	1.5		
Deflection angle:	90°		
Standard pointer:	Black tubular		
Operating temperature:	0-50°C		
Calibration position:	For vertical mounting		

Ordering information

Order Code	Size	Range	Rec. Price £:		
			5+	10+	25+ 50+
METERS					
AM25UA100	AM25	0-100µA DC			
AM25MA1	AM25	0-1mA DC			
AM25MV75	AM25	0-75mV DC			
AM35UA100	AM35	0-100µA DC			
AM35MA1	AM35	0-1mA DC			
AM35MV75	AM35	0-75mV DC			
AM45UA100	AM45	0-100µA DC			
AM45MA1	AM45	0-1mA DC			
AM45MV75	AM45	0-75mV DC			
ANXILLARIES					
CAM25	AM25	Black Cover			
BAM25	AM25	Black Bezel			
SAM25/0	AM25	Blank scale			
SAM25/10	AM25	0-10 scale			
SAM25/30	AM25	0-30 scale			
SAM25/100	AM25	0-100 scale			
CAM35	AM35	Black Cover			
BAM35	AM35	Black Bezel			
SAM35/0	AM35	Blank scale			
SAM35/10	AM35	0-10 scale			
SAM35/30	AM35	0-30 scale			
SAM35/100	AM35	0-100 scale			
CAM45	AM45	Black Cover			
BAM45	AM45	Black Bezel			
SAM45/0	AM45	Blank scale			
SAM45/10	AM45	0-10 scale			
SAM45/30	AM45	0-30 scale			
SAM45/100	AM45	0-100 scale			

AVAILABLE DIRECT FROM ANDERS