



MSA-0110



Die profile



Crimp profile

The MSA-0110 is a precision, ratchet crimp tool designed to provide consistent and reliable crimp connections on Transparent / Green / Red insulated terminals on wires ranging from .

Easy to use

Open the tool. Insert terminal in correct nest. Close tool until terminal fastened. Insert wire into terminal. Close tool until ratchet release. Attention: To release ratchet mechanism, push the trigger.

Calibration

To calibrate this tool the pre-load has to be measured. Gauge is required to ensure that the die is according to specification. For more information; See instruction sheet.

- The dies mark to terminal so that they can be inspected for correct use of the tool.
- Ergonomic handles allowing two handed operation for powerful, low effort crimping.
- Ratchet action to ensure full crimp cycle with safety release.
- Durable - minimum of 50,000 cycles.
- Tool is factory set with a precise eccentric cam adjustment function to guarantee performance.

Technical data

Prod. code:	MSA-0110
Length:	212 mm / 8,35"
Height:	72 mm / 2,83"
Weight:	470 gr / 1,04 lbs
Connector:	Pre-insulated
Description:	Transparent / Green / Red
Wire size:	26-16 AWG

Distributors address info