

Soldering Irons and Tips



Electronically Controlled Low Voltage Soldering Irons



LT Soldering tips: see page 79 / 80




Order No.	Model	Description
005 15 147 99	WDH 10P	WDH 10 Nitrogen Stop and go safety rest-kit for soldering iron WSP 80 For special solder applications with lead free solder. The WDH 10P nitrogen stop and go safety rest-kit gives the possibility to upgrade the Weller soldering iron WSP 80 to a nitrogen iron. Through the special nitrogen barrel the gas fed to the solder tip and becomes heated up. The Stop+Go safety rest starts the gas flow when the iron is removed and stops it when the iron is replaced. With a spherical valve the gas flow could be regulated. The nitrogen could be taken from pressure bottle, tank, or a nitrogen generator. For a good soldering result the purity from nitrogen should be 5.0.
consist of:		
	WDH 10P	Stop+Go safety rest for nitrogen use spherical valve Pressure air tube 4 mm Nitrogen barrel for WSP 80 (Set)
005 87 448 47		



LT Soldering tips: see page 79 / 80

Order No.	Model	Description
005 33 131 99	MPR 80	Soldering set Peritronic 80 W, 24 V The Peritronic soldering pencil gives all-round vision when making intricate connections. Adjustable head for maximum view.
consists of:		
005 29 163 99	MPR 80	Soldering iron 80 W, 24 V Peritronic with soldering tip LT B
005 15 033 99	KH 25P	Safety rest

Soldering Tips for WP 80, WSP 80, FE 75 and MPR 80



Order No.	Model	Description	Width A	Thickness B	max.Length L
005 44 494 99	LT 1SC	Chisel tip, single packaged	0,4 mm	0,15 mm	15,0 mm
005 44 494 00	LT 1SC	Chisel tip, bulk	0,4 mm	0,15 mm	15,0 mm
005 44 437 99	LT H	Chisel tip, single packaged	0,8 mm	0,4 mm	13,5 mm
005 44 412 00	LT H	Chisel tip, bulk	0,8 mm	0,4 mm	13,5 mm
005 44 412 11	LT H	Chisel tip, packaged 100 pcs.	0,8 mm	0,4 mm	13,5 mm
005 44 403 00	LT A	Chisel tip, bulk	1,6 mm	0,7 mm	13,5 mm
005 44 403 11	LT A	Chisel tip, packaged 100 pcs.	1,6 mm	0,7 mm	13,5 mm
005 44 405 00	LT B	Chisel tip, bulk	2,4 mm	0,8 mm	13,5 mm
005 44 405 11	LT B	Chisel tip, packaged 100 pcs.	2,4 mm	0,8 mm	13,5 mm
005 44 407 00	LT C	Chisel tip, bulk	3,2 mm	0,8 mm	13,5 mm
005 44 407 11	LT C	Chisel tip, packaged 100 pcs.	3,2 mm	0,8 mm	13,5 mm
005 44 409 00	LT D	Chisel tip, bulk	4,6 mm	0,8 mm	13,5 mm
005 44 409 11	LT D	Chisel tip, packaged 100 pcs.	4,6 mm	0,8 mm	13,5 mm
005 44 448 99	LT DLL	Chisel tip, single packaged	4,6 mm	0,8 mm	13,5 mm
005 44 448 00	LT DLL	Chisel tip, bulk	4,6 mm	0,8 mm	13,5 mm
005 44 413 00	LT K	Chisel tip long, bulk	1,2 mm	0,4 mm	21,0 mm
005 44 413 11	LT K	Chisel tip long, packaged 100pcs.	1,2 mm	0,4 mm	21,0 mm
005 44 414 00	LT L	Chisel tip long, bulk	2,0 mm	1,0 mm	21,0 mm
005 44 414 11	LT L	Chisel tip long, packaged 100pcs.	2,0 mm	1,0 mm	21,0 mm
005 44 415 00	LT M	Chisel tip long, bulk	3,2 mm	1,2 mm	21,0 mm
005 44 415 11	LT M	Chisel tip long, packaged 100pcs.	3,2 mm	1,2 mm	21,0 mm