

Stripping and cutting tools

Stripping and cutting tools

- For flexible and massive conductors with PVC-insulation
- Stripping length adjustable with shoulder
- automatic opening of the clamping jaws after stripping
- no splicing of the single conductor
- adjustable to different insulation thicknesses
- cable with double insulation in two processing steps without special adjustment
- Blade-device free from float and self-adjustable
- long durability
- optimised ergonomically design

stripax®



stripax® 16



Stripping and cutting tool for flexible conductors with PVC-insulation of 0.08...6 mm² (~AWG 28...10)

- No damaging of the conductor due to special, self-adjustable stripping blades
- Processing of multi-conductors, with thin flat ribbon cables even multiple conductors in one operation

Stripping and cutting tool for flexible and massive conductors with PVC-insulation of 6...16 mm² (~AWG 10... 6)

- Cutting of flexible and massive conductors up to 6 mm² (AWG 10)
- No damaging of the conductor due to special blade forms

Technical data

Max. stripping performance		stripax®	stripax® 16
Cable model		flexible & solid conductors with PVC insulation	flexible & solid conductors with PVC insulation
Conductor cross-section	mm ²	0.08 ... 6	6 ... 16
Conductor diameter	mm		
Max. stripping length	mm	20	20
Adjustable depth of cut	mm		
Cutting performance			
Max. cutting performance	mm ²	6	6
Tool data			
Length	mm	190	190
Weight	g	155	155
Information			

Ordering data

Version	Type	Qty.	Order No.	Type	Qty.	Order No.
	STRIPAX	1	9005000000	STRIPAX 16	1	9005610000
Information						

Accessories

Type	Qty.	Order No.	Type	Qty.	Order No.
Cleaning brush	5	9005450000	Cleaning brush	5	9005450000
Spare stripping blades	1	9054030000	Spare stripping blades	1	9054080000
Information					