


## Pan head self tapping screws - Slotted - Pointed



DIN 7981 C  
BS 4174 AB

### Materials and Finishes

Case hardened steel/Zinc & clear de-embrittled  
Stainless steel/Self colour

### Dimensions

Dimension	2.2	2.9	3.5	3.9	4.2	4.8	5.5	6.3
d	2.2	2.9	3.5	3.9	4.2	4.8	5.5	6.3
d	No.2	No.4	No.6	No.7	No.8	No.10	No.12	No.14
D max	4.2	5.6	6.9	7.5	8.2	9.5	10.8	12.5
H max	1.35	1.75	2.1	2.25	2.45	2.8	3.2	3.65

### Head Dimensions

		Thread (d)							
		2.2	2.9	3.5	3.9	4.2	4.8	5.5	6.3
Length (L)	4.8								
	6.4		ST	ST					
	7.9		ST	ST					
	9.5	ST	ST	ST	ST	ST	ST		
	12.7	ST	ST	ST		ST	ST	ST	ST
	15.9		ST	ST	ST	ST	ST	ST	ST
	19		ST	ST	ST	ST	ST	ST	ST
	22.2		ST	ST		ST			
	25.4		ST	ST	ST	ST	ST	ST	ST
	31.8			ST	ST	ST	ST	ST	ST
	38			ST	ST	ST	ST	ST	ST
	44.5								
50					ST	ST	ST	ST	

ST - Steel, Zinc & clear de-embrittled