


Nylon insert nuts - Type T - Thin



DIN 985/DIN 6924

Materials and Finishes

Steel/Zinc & clear
Stainless steel/Self colour

Dimensions

	M3	M4	M5	M6	M8	M10	M12	M14	M16	M18 ¹	M20 ¹
d											
m	2.4	2.9	3.2	4	5.5	6.5	8	9.5	10.5	13	14
s	5.5	7	8	10	13	17	19	22	24	27	30
h	4	5	5	6	8	10	12	14	16	18.5	20
e approx.	6.1	7.7	8.8	11.1	14.4	19.0	21.1	24.5	26.8	29.6	33.0