

PT-2030VP

TZ-Tape



Upon registration

Desktop Electronic Labeller



Copy

It's quick, versatile...and makes it easier than ever to organise your office! The neat desktop design with its easy to read large LCD screen produces a huge range of hard-wearing labels, with a huge range of font sizes, symbols and styles for added flexibility. It also features Brother's new Label Collection, with 55 pre-made, professional designs in 18 languages.

Catalogue Spec

- Durable – labels up to 18mm, able to handle extreme conditions
- Easy to use QWERTY keyboard
- Preview your design easily with the large LCD screen
- Space-saving compact, stylish design
- Convenient cutter for accurate label length
- Save time with up to 10mm per second printing
- Get creative, with customised labels printed direct from your PC
- Everything you need – includes 18mm black on white tape (4m)

What's in the Box

- 1x 18mm Tape (as advised above)
- AD-24ES (Energy Star) Adapter
- Carry Case (Navy Blue)
- User Guide

INPUT DEVICE	
Keyboard	QWERTY
DISPLAY	
Display	Graphic (16 chrs x 3 line) same as 2100 LCD
Language Support	English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finnish, Hungarian, Czech, Polish, Romanian, Slovene, Slovak, Croatian, Turkish
PRINTING	
Print Height	15.8 mm
Print Speed	10 mm / sec
Print Resolution	180 dpi / 128 dots
FEATURES	
Multi Line Printing	5 lines
Multi Block Printing	Yes (Max. 5 blocks)
Copy Printing	Yes (1-9)
Bar Code	Yes (9 kinds)
Mirror Printing	Yes
Numbering	Yes (1-9)
Vertical Printing	Yes (in the style setting)
Underline	Yes (underline / strikeout)
Framing	16 kinds
Font variations	4 kinds (Helsinki/Brussels/Florida/Calgary)
Font style variations	10 kinds (Normal/Bold/Outline/Shadow/Solid/Italic/Italic Bold/Italic Outline/Italic Shadow/Italic Solid/Vertical)
Font size variations	7 kinds (Auto/6/9/12/18/24/36/42pt)
Font width variations	4 kinds (x1/2, x2/3, x1, x2)
Number of Characters	462
Number of Symbols	253
Number of Auto Formats	31
Tape Cut	Manual
Preview	Yes
Label Length Setting	Yes (30 - 300mm)
Label Collection	55 kinds
Label Collection DL Feature	No
DECO MODE	No
Text Reminder	No
Time & Date	No
MEMORY	
Memory	1800 chrs (9 areas)
POWER SUPPLY	
Power Supply	AAA x 6 pcs AC adapter AD-24ES
SIZE	
Dimensions	58mm (H) x 164mm (W) x 216mm (D)
Weight	0.57kg
SUPPLIES	
Tape Cartridge	TZ Tape
Tape width variations	3.5, 6, 9, 12, 18mm
PC CONNECTION	
Operating System	-
Interface	No
Label Editing Software	-