

# SUB-MINIATURE JACKS & PLUGS 150/3150 SERIES TRS/TTM



## Sub-miniature Jacks & Plugs

Sub-miniature concentric twinax/triax connectors increase packing density up to 246%. They are designed for high density applications where digital, video pair or baseband noise-free guarded circuits are required. The 3-lug, 4-lug, and threaded versions improve mechanical stability and provide "error-free" redundant data bus capabilities. The wrench crimp version accommodates cables with other jacket diameters up to .215" and the tool crimp versions up to .250".

PL155-29 Shown

**CABLE PLUG  
WRENCH CRIMP**

3-lug  
4-lug  
Threaded

**PL155-<sup>△</sup>  
PL155FL-<sup>△</sup>  
PL3155-<sup>△</sup>**

BJ159-29 Shown

**BULKHEAD JACK  
REAR MOUNT, WRENCH CRIMP**

3-lug  
4-lug  
Threaded

**BJ159-<sup>△</sup>  
BJ159FL-<sup>△</sup>  
BJ3159-<sup>△</sup>**

Mounting Hole: D4.125

PL155AC-207 Shown

**CABLE PLUG  
TOOL CRIMP**

3-lug  
4-lug  
Threaded

**PL155AC-<sup>△</sup>  
PL155ACFL-<sup>△</sup>  
PL3155AC-<sup>△</sup>**

BJ159AC Shown

**BULKHEAD JACK  
REAR MOUNT, TOOL CRIMP**

3-lug  
4-lug  
Threaded

**BJ159AC-<sup>△</sup>  
BJ159ACFL-<sup>△</sup>  
BJ3159AC-<sup>△</sup>**

Mounting Hole: D4.125

PLR3155AC-201 Shown

**RIGHT ANGLE  
CABLE PLUG  
TOOL CRIMP**

3-lug  
4-lug  
Threaded

**PLR155AC-<sup>△</sup>  
PLR155ACFL-<sup>△</sup>  
PLR3155AC-<sup>△</sup>**

CJ150-29 Shown

**CABLE JACK  
WRENCH CRIMP**

3-lug  
4-lug  
Threaded

**CJ150-<sup>△</sup>  
CJ150FL-<sup>△</sup>  
CJ3150-<sup>△</sup>**

CJ150AC-207 Shown

**CABLE JACK  
TOOL CRIMP**

3-lug  
4-lug  
Threaded

**CJ150AC-<sup>△</sup>  
CJ150ACFL-<sup>△</sup>  
CJ3150AC-<sup>△</sup>**

<sup>△</sup>- Refers to Cable Group Table see pages 91-133. "D" mounting holes see page 54