

MONITOR SPEAKERS

1C

Technical Specifications

GB

Version 1.0 April 2006



www.behringer.com



MONITOR SPEAKERS 1C

Ultra-Compact Monitor Speakers

- ▲ Multi-purpose 2-way studio monitors ideally suited for fixed installation, multimedia, home recording studio, audio/video production and surround-sound systems
- ▲ High power handling capability (100 W / IEC268-5) produces full-range output with extremely low distortion
- ▲ Powerful 5 ½" woofer with extremely light-weight cellulose cone and high-resolution ½" tweeter
- ▲ Ultra-linear frequency range from 60 Hz to 23 kHz
- ▲ Phase-optimized and high-precision crossover for absolute phase linearity
- ▲ Auto overload protection prevents tweeter damage and resets automatically
- ▲ Bracket for wall/ceiling mounting included
- ▲ High-quality components and exceptionally rugged construction ensure long life
- ▲ Conceived and designed by BEHRINGER Germany

SPECIFICATIONS

Connector type	Clip terminal
Wire diameter	< 4 mm
Power capacity (prg.)	100 W (IEC 268-5)
Impedance	4 Ω
Frequency range	60 Hz to 23 kHz (-10 dB)
Nominal sound pressure level (SPL)	86 dB*W/m (program, bandwidth 100 - 5000 Hz on axis, full space)
Max. short term acoustic output	112 dB @ 1m (on axis, half space)
Tweeter	½"
Woofer	5 ½"
Crossover frequency	5000 Hz
Dimensions (H x W x D)	8.9" x 5.9" x 5.6" (225 x 150 x 142 mm)
Weight	approx. 4 lbs each (1.8 kg each)

BEHRINGER is constantly striving to maintain the highest professional standards. As a result of these efforts, modifications may be made from time to time to existing products without prior notice. Specifications and appearance may differ from those listed or illustrated.

Technical specifications and appearance subject to change without notice. The information contained herein is correct at the time of printing. The names of companies, institutions or publications pictured or mentioned and their respective logos are registered trademarks of their respective owners. Their use neither constitutes a claim of the trademarks by BEHRINGER® nor affiliation of the trademark owners with BEHRINGER®. BEHRINGER® accepts no liability for any loss which may be suffered by any person who relies either wholly or in part upon any description, photograph or statement contained herein. Colours and specification may vary slightly from product. Products are sold through our authorised dealers only. Distributors and dealers are not agents of BEHRINGER® and have absolutely no authority to bind BEHRINGER® by any express or implied undertaking or representation. No part of this manual may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording of any kind, for any purpose, without the express written permission of BEHRINGER Spezielle Studioteknik GmbH. BEHRINGER® is a registered trademark.

ALL RIGHTS RESERVED. © 2006 BEHRINGER Spezielle Studioteknik GmbH,
Hanns-Martin-Schleyer-Str. 36-38, 47877 Willich-Münchheide II, Germany.
Tel. +49 2154 9206 0, Fax +49 2154 9206 4903