


# Plug-type compact connector ST 18/3poles Female / male parts for "snap-in mounting": without screw connection

mounting size 33 × 15.6 mm



rated voltage 250 V~

rated current 16 A

rated cross section 2.5 mm<sup>2</sup>



insulating length 8 mm  
mounting size 33 × 15.6 mm  
material thickness 0.5–1.5 mm



For fast mounting of female/male plug connectors, e. g. in cases of lighting devices or in plug boxes the snap-in version can be interlocked without using screws. The case opening is cleanly covered.

Connecting the terminals is possible in a screwless version as well as with screws.

Using a locking slide, the ready-made and the crimp version of ST 18 can be interlocked.

## male part

for "snap-in mounting"

colour: black

93.032.9053.0

100

colour: white

93.032.9058.0

100

## female part

for "snap-in mounting"

colour: black

93.031.9053.0

100

colour: white

93.031.9058.0

100

## locking slide (to be ordered separately)

suitable for ready-made ST 18/3

colour: black

05.584.0153.0

100

colour: white

05.584.0153.2

100