



## INDUSTRIAL | MARINE BELL


### ACOUSTIC

## Acoustic Signals Industrial & Marine Bells > IP66 Series

### Product overview

The IP66 bell is a fully enclosed signal bell. It is suitable for areas where harsh weather conditions exist, such as

exposed outdoor locations, marine applications and wash/hose down areas. The solenoid driven mechanism produces a clear, loud tone.



#### Features

High quality penetrating sound

Weatherproof to IP66

#### Material

Steel gong



Code No:	Voltage:	Current:
A6B-12DC-IP66	12v Dc ---	0.06 A
A6B-24DC-IP66	24v Dc ---	0.03 A
A6B-115AC-IP66	115v Ac ~	0.90 A
A6B-230AC-IP66	230v Ac ~	0.50 A



## INDUSTRIAL BELL


### ACOUSTIC

## Acoustic Signals Industrial Bells > Adaptabel Series

### Product overview

The Adaptabel range is a high quality solenoid driven bell designed for use in commercial, industrial and transportation applications. With a choice of three gong sizes, this unit delivers

a clear, loud ring which is free from mechanical clatter. The bigger the gong, the deeper, louder and more penetrating the sound. When fitted with the optional back box, the units are weatherproof and suitable for mounting in exposed locations. Red version available in 6" 24v Dc.



#### Features

Supplied with a universal mounting plate for all installation options

Rugged die-cast construction

Robust and reliable

Wide range of voltages available

Optional IP65 weatherproof back box

#### Material

Steel gong



Code No:	Voltage:	Size:	dB:	Current:
A4B-K-12DC	12v Dc ---	101mm/4"	99dB	125 mA
A4B-K-24AC	24v Ac ~	101mm/4"	99dB	-
A4B-K-24DC	24v Dc ---	101mm/4"	99dB	62 mA
A4B-K-115AC	115v Ac ~	101mm/4"	99dB	34 mA
A4B-K-230AC	230v Ac ~	101mm/4"	99dB	22 mA
A6B-K-12DC	12v Dc ---	152mm/6"	101dB	125 mA
A6B-K-24AC	24v Ac ~	152mm/6"	101dB	-
A6B-K-24DC	24v Dc ---	152mm/6"	101dB	62 mA
A6B-K-24DCR	24v Dc ---	152mm/6"	101dB	-
A6B-K-115AC	115v Ac ~	152mm/6"	101dB	34 mA
A6B-K-230AC	230v Ac ~	152mm/6"	101dB	22 mA
A8B-K-24DC	24v Dc ---	203mm/8"	102dB	62 mA
A8B-K-115AC	115v Ac ~	203mm/8"	102dB	34 mA
A8B-K-230AC	230v Ac ~	203mm/8"	102dB	22 mA

AB-K-WPBB Weatherproof backbox\* Cabling entries x 3 (3/4"NPT or M20)

Kg 1.00

dB 103

°C -30+50

IP 66

CONTINUOUS

INDUSTRIAL

Kg 1.0/1.4/2.3

dB 99 - 102

°C -35+66

IP 44/65\*

CONTINUOUS

INDUSTRIAL

APPROVAL AND CONFORMITIES



MARINE

APPROVAL AND CONFORMITIES

