




KF PV 0100


empty box

- insulated box for photovoltaic plants of up to AC 690 V / DC 1000 V
- "Outdoor - harsh environment and (or) outdoor"
- box walls without knockouts

box walls



Dimension drawing



protection class

II

degree of protection:

IP 66

material:
mounting width

thermoplastic
59 mm

mounting height

66 mm

max. installation depth

37 mm

colour:

black RAL 9011

cable entry

wall surface can be drilled individually for cable entry max. M 20

height:

88 mm