




Connecting cables
M12 to M8 LED



Ordering data

Male, straight - Female, angled	
PVC	1.5 m
PUR	1.5 m
PUR halogen-free	1.5 m
PUR halogen-free yellow	1.5 m
Note	

2 LEDs

3-pole

Type	Order No.
SAIL-M12GM8W-3L1.5V	1962290150
SAIL-M12GM8W-3L1.5U	9457760150
SAIL-M12GM8W-3L1.5Q	1962270150
SAIL-M12GM8W-3L1.5QGE	1093110150
Other versions on request	

2 LEDs

4-pole

Type	Order No.
SAIL-M12GM8W-4L1.5V	1962300150
SAIL-M12GM8W-4L1.5U	1906430150
SAIL-M12GM8W-4L1.5Q	1962280150
SAIL-M12GM8W-4L1.5QGE	1093130150
Other versions on request	

Standard cable lengths

All cables listed under the ordering data have a length of 1.5 metres. The last four ordering digits must be changed when ordering other standard cable lengths.	1.5 m	xxxxx0150
	3.0 m	xxxxx0300
	5.0 m	xxxxx0500
	10.0 m	xxxxx1000

Technical data

Rated current	4 A
Protection class	IP 67
Core cross-section	0.25 mm ²
Contact surface	gold-plated
Temperature range of housing	-25...+85 °C
Rated voltage	60 V (3-pole) / 30 V (4-pole)
(acc. to VDE standard 0110 ISO group C)	

Chapter W includes additional technical specifications for the cable

Dimensioned drawing

