

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0022011043](#)  
**Status:** **Obsolete**  
**Overview:** [kk](#)  
**Description:** 2.50mm (.098") Pitch KK® Wire-To-Board Housing, Female, Friction Lock, for 4809 Crimp Terminal, 4 Circuits

**Documents:**  
[Drawing \(PDF\)](#)

**Agency Certification**

CSA	LR19980
TUV	R72090224
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">5051</a>
Application	Signal
Overview	<a href="#">kk</a>
Product Name	KK®

**Physical**


Circuits (maximum)	4
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm (.098")
Stackable	No
Temperature Range - Operating	-40°C to +105°C

**Material Info**

Old Part Number	5051-04M
-----------------	----------

**Reference - Drawing Numbers**

Product Specification	PS-99020-0088
Sales Drawing	SDE-5051-NM-*



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[5051Series](#)

**Mates With**

[5045 Vertical Header](#), [5046 Right Angle Header](#)

**Use With**

[4809](#)