



Actual information about approvals can be found on
<http://www.schurter.com/approvals>



6600-4

F



Description

- Panel mount:
Snap-in version from front side
- Outlet, Pin temperature 70 °C, Protection class I
- Solder terminals or quick connect terminals

Other versions on request:

- other panel thickness


Technical data

Ratings IEC	10 A / 250 VAC; 50 Hz
Ratings UL/CSA	15 A / 250 VAC; 60 Hz
Dielectric strength	> 2 kVAC between L-N > 2 kVAC between L/N-PE (1 min/50 Hz)
Allowable operation temp.	-25 °C to 70 °C
Degree of protection	from front side IP30 acc. to IEC 60529
Protection class	Suitable for appliances with protection class I acc. to IEC 61140

Terminals	Solder terminals or quick connect terminals
Panel thickness s	Snap-in: 1/1.2/1.5/2/2.5/3 mm
Materials: Housing	Thermoplastic, black, UL 94V-0
Appliance-inlet /-outlet	F acc. to IEC/EN 60320-2-2, UL 498, CSA C22.2 no. 42 (for cold condition) pin-temperature 70 °C, 10 A, Protection class I

Dimensions

6600-4



E: solder terminals 3.5x0.8mm	24.1mm
E: quick connect terminals 4.8x0.8mm	26.5mm
E: quick connect terminals 6.3x0.8mm	27.5mm
S: 1.0; 1.2; 2.0; 2.5; 3.0 mm	

Variants

Order Number	Panel mounting	Panel thickness s [mm]	Terminals
6600.4210	Snap-in	1	Quick connect terminals 4.8 x 0.8 mm
6600.4212	Snap-in	1.2	Quick connect terminals 4.8 x 0.8 mm
6600.4215	Snap-in	1.5	Quick connect terminals 4.8 x 0.8 mm
6600.4220	Snap-in	2	Quick connect terminals 4.8 x 0.8 mm
6600.4225	Snap-in	2.5	Quick connect terminals 4.8 x 0.8 mm
6600.4230	Snap-in	3	Quick connect terminals 4.8 x 0.8 mm
6600.4310	Snap-in	1	Quick connect terminals 6.3 x 0.8 mm
6600.4312	Snap-in	1.2	Quick connect terminals 6.3 x 0.8 mm
6600.4315	Snap-in	1.5	Quick connect terminals 6.3 x 0.8 mm
6600.4320	Snap-in	2	Quick connect terminals 6.3 x 0.8 mm
6600.4325	Snap-in	2.5	Quick connect terminals 6.3 x 0.8 mm
6600.4330	Snap-in	3	Quick connect terminals 6.3 x 0.8 mm
6600.4110	Snap-in	1	Solder terminals 3.8 x 0.8 mm
6600.4112	Snap-in	1.2	Solder terminals 3.8 x 0.8 mm
6600.4115	Snap-in	1.5	Solder terminals 3.8 x 0.8 mm
6600.4120	Snap-in	2	Solder terminals 3.8 x 0.8 mm
6600.4125	Snap-in	2.5	Solder terminals 3.8 x 0.8 mm
6600.4130	Snap-in	3	Solder terminals 3.8 x 0.8 mm

1) Minimum order quantity for rivet mount types required
Cord retaining clamp and insulation cover see accessoires

Packaging unit

50 Pcs

Accessories

ACCESSORIES