



### Main

Enclosure type	Weatherproof enclosure
Range of product	Kaedra
Device short name	Kaedra for modular devices
Accessories included with enclosure	1 marking kit 2 terminal blocks 4 holes

### Complementary

Enclosure mounting	Surface
Type of front cover	Transparent
Number of horizontal rows	1
Number of 18 mm modules per row	6
Total number of 18 mm modules	6
Type of rail	DIN
Number of pre-cutouts PG ISO	3
Number of terminal blocks	2 4
Distribution block outgoers	4 x 10 mm <sup>2</sup> 4 x 16 mm <sup>2</sup>
Locking options description	Optional keylock
Enclosure material	Plastic
Width	159 mm
Height	200 mm
Depth	112 mm
Colour	Light grey RAL 7035 enclosure Transparent green door

### Environment

Standards	EN 50102 EN 50262 IEC 60439-3 IEC 60529 IEC 60695-2-1 IEC 670
Fire resistance	650 °C IEC 60695-2-1
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK09 EN 50102
Electrical shock protection class	Class II
Ambient air temperature for operation	-25...60 °C
RoHS EUR conformity date	0648
RoHS EUR status	Compliant