

For more Information  
please call

1-800-Belden1



### Description:

Tinned copper conductor, PVC insulation. Covers insulated wire for internal wiring of meters, panels, and electrical or electronic equipment. Temperatures to 105°C.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Conductors	AWG	Stranding	Conductor Material
1	22	7x30	TC - Tinned Copper

#### Insulation

##### Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.254

#### Overall Insulation

#### Overall Cabling

Overall Nominal Diameter: 1.270 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Military Specification:	MIL-W-16878/1
MIL Spec Rating:	600 V, 105°C

#### Plenum/Non-Plenum

Plenum (Y/N): No

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8503 001100	30 MT	0.181 KG	BROWN		22 STR PVC BRN
8503 0011000	305 MT	1.814 KG	BROWN	P	22 STR PVC BRN
8503 002100	30 MT	0.181 KG	RED		22 STR PVC RED
8503 0021000	305 MT	1.814 KG	RED	P	22 STR PVC RED
8503 003100	30 MT	0.181 KG	ORANGE		22 STR PVC ORG

## METRIC MEASUREMENT VERSION

### 8503 Hook-up/Lead - (Type B) MIL-W-16878/1-PVC

8503 0031000	305 MT	1.814 KG	ORANGE	P	22 STR PVC ORG
8503 004100	30 MT	0.181 KG	YELLOW		22 STR PVC YEL
8503 0041000	305 MT	1.814 KG	YELLOW	P	22 STR PVC YEL
8503 005100	30 MT	0.181 KG	GREEN, DARK		22 STR PVC GRN
8503 0051000	305 MT	1.814 KG	GREEN, DARK	P	22 STR PVC GRN
8503 006100	30 MT	0.181 KG	BLUE, LIGHT		22 STR PVC LBLU
8503 0061000	305 MT	1.814 KG	BLUE, LIGHT	P	22 STR PVC LBLU
8503 007100	30 MT	0.181 KG	VIOLET		22 STR PVC VIO
8503 0071000	305 MT	1.814 KG	VIOLET	P	22 STR PVC VIO
8503 008100	30 MT	0.181 KG	GRAY		22 STR PVC GRY
8503 0081000	305 MT	1.814 KG	GRAY	P	22 STR PVC GRY
8503 009100	30 MT	0.181 KG	WHITE		22 STR PVC WHT
8503 0091000	305 MT	1.814 KG	WHITE	P	22 STR PVC WHT
8503 010100	30 MT	0.181 KG	BLACK		22 STR PVC BLK
8503 0101000	305 MT	1.814 KG	BLACK	P	22 STR PVC BLK
8503 0141000	305 MT	1.814 KG	WHITE/BLACK	A	22 STR PVC WHT/BLK
8503 0151000	305 MT	1.814 KG	WHITE/RED	A	22 STR PVC WHT/RED
8503 0161000	305 MT	1.814 KG	WHITE/GREEN	A	22 STR PVC WHT/GRN
8503 0171000	305 MT	1.814 KG	WHITE/YELLOW	A	22 STR PVC WHT/YEL
8503 0181000	305 MT	1.814 KG	WHITE/BLUE	A	22 STR PVC WHT/BLU
8503 0191000	305 MT	1.814 KG	WHITE/BROWN	A	22 STR PVC WHT/BRN
8503 0211000	305 MT	1.814 KG	WHITE/GRAY	A	22 STR PVC WHT/GRY
8503 0221000	305 MT	1.814 KG	WHITE/VIOLET	A	22 STR PVC WHT/VIO

#### Notes:

A = STOCKED STRIPE COLORS.

P = STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M' FOR 1 OR 2 STRIPES. 10000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL

Revision Number: 1    Revision Date: 05-14-2007

© 2011 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.