

For more Information
please call

1-800-Belden1



Description:

Tinned copper conductor, conductive polyethylene (Korona-Guard) over inner conductor provides uniform distribution of voltage stresses, polyethylene insulated. Red PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	18	16x30	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PE - Polyethylene	1.4478

Other: .008 in. conductive polyethylene over stranding.

Jacket

Jacket Material: PVC - Polyvinyl Chloride

Jacket Thickness: .015

Overall Insulation

Overall Cabling

Overall Nominal Diameter: 5.283 mm

Mechanical Characteristics (Overall)

Non-UL Temperature Rating: 80°C

Bulk Cable Weight: 29.764 Kg/Km

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 10/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Max. Operating Voltage - Other:

Voltage	Description
---------	-------------

40,000 V	DC
11,000 V	AC (60 Hertz)

Breakdown Voltage: 80, 000 DC

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8866 002U500	152 MT	5.216 KG	RED		#18 STR 40 KV HIGH VOLT
8866 002100	30 MT	1.225 KG	RED		#18STR 40 KV HIGH VOLT
8866 002500	152 MT	4.536 KG	RED	C	#18 STR 40 KV HIGH VOLT

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 06-03-2011

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.