

For more Information
please call

1-800-Belden1



Description:

EPDM high temperature lead wire. 150C EPDM wire is recommended for Class 130(B) , 155(F) and also in some 180(H) systems. It's UL Recognized under Style 3374 as 150C-600V Appliance Wiring Material. The CSA Listing, as a coil lead, is 125C, 600V.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	12	65x30	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material
EPDM - Ethylene Propylene Diene Monomer Rubber

Overall Insulation

Overall Cabling

Overall Nominal Diameter: 4.826 mm

Mechanical Characteristics (Overall)

UL Temperature Rating: 125°C (UL AWM Style 3340), 125°C (UL AWM Style 3374), 150°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL AWM Style: UL Style 3340 (600 V 125°C), UL Style 3374 (600 V 125°C)

UL Rating: 600 V, 150°C

CSA Rating: 600 V, 125°C

CSA Type: CL1254

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Max. Operating Voltage - UL:

Voltage
600 V RMS (UL AWM Style 3340)
600 V RMS (UL AWM Style 3374)

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
37112 002500	152 MT	7.484 KG	RED	C F	#12 STR EPDM 150C 600V
37112 0103000	914 MT	47.627 KG	BLACK	C I	#12STR EPDM 150C 600VBLK
37112 010500	152 MT	7.484 KG	BLACK	C F	#12 STR EPDM 150C 600V
37112 0105000	1,524 MT	77.111 KG	BLACK	C M	#12 STR EPDM BLK

Notes:

C = CRATE REEL PUT-UP.

F = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'

I = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 200'

M = FINAL PUT-UP LENGTH MAY VARY -10% TO +0% FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 05-14-2007

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.