


## Prototyping Boards SMD



### RE435-LF



- EPOXY fibre-glass FR4 0.70 mm double-sided 35 µm CU (pth)
- chem. SN
- SMD breadboard 1.27 x 1.27 mm (1/40")
- 39 x 59 single-hole conductors 1.0 mm<sup>2</sup>
- hole dia 0.35 mm
- suitable for all SMD components
- size 53 x 95 mm