


Prototyping Boards SMD



RE436-LF



- EPOXY fibre-glass FR4 1.50 mm double-sided 35 µm CU (pth)
- chem. SN
- mixed construction
- SMD breadboard 1.27 x 1.27 mm (1/40")
- 40 x 60 single-hole conductors 1.0 mm²
- hole dia 0.35 mm
- suitable for all SMD components
- two breadboards 2.54 x 2.54 mm (1/20") 17 x 32 and 18 x 32 single-hole conductors 2.0 mm²
- hole dia 1.0 mm
- connector 32 / 64 / 96 - channel
- DIN 41612 type C
- size 100 x 160 mm