


Prototyping Board



RE521-HP



- SRBP-paper FR2 1.5 mm single-sided 35 µm CU
- organic soldering protection (OSP)
- 37 continuous strips with 57 borings
- hole spacing 2.54 x 2.54 mm
- hole dia 1.0 mm
- with additional print on component side
- connector 32-channel DIN 41612
- grid 5.08 mm type D
- size 100 x 160 mm