


## Prototyping Board



### RE200-HP



- SRBP-paper FR2 1,5 mm single-sided 35 µm CU
- organic soldering protection (OSP)
- 38 x 61 single-hole conductor 2,2 mm Ø
- hole spacing 2,54 x 2,54 mm
- hole dia 1,0 mm
- size 100 x 160 mm