


Prototyping Board



RE840-LF



- EPOXY fibre-glass FR4 1.5 mm single-sided 35 µm CU
- hot air leveling (HAL-leadfree)
- 53 x 89 single-hole conductor 2.2 mm Ø
- hole spacing 2.54 x 2.54 mm
- hole dia 1.0 mm
- connector 32/ 64/ 96-channel
- DIN 41612 type C
- size 160 x 233.40 mm