


## Extender Card



### RE960C96/1LF



- extender cards for 19"-systems DIN 41612 C96 a+b+c
- EPOXY fibre-glass FR4 1.5 mm single-sided 70 µm CU
- solder stop mask
- removable jumpers and two measuring posts for each track
- signaling line 2 - 31
- large signalling line 1 + 32
- switching voltage 10mV - 60V
- switching current 0.5A at 24V
- rest current at 20°C, max 2 A
- contact resistance 20 mOhm
- extender card: 100% electronically tested
- additional print at component side
- connector 32/ 64/ 96-channel DIN 41612 type C