


## Prototyping Board



### RE317-LF



- EPOXY fibre-glass FR4 1.5 mm single-sided 35 µm CU
- hot air leveling (HAL-leadfree)
- 37 x 55 single-hole conductor 2.0 mm dia
- hole spacing 2.54 x 2.54 mm
- hole dia 1.0 mm
- connector 32-channel
- DIN 41612
- grid 5.08 mm type D
- size 100 x 160 mm