


## QFP Multiadapter 144



## RE471



- EPOXY resin FR4 1.50 mm double-sided 35 µm CU (pth)
- chem. NI/AU
- Two universal QFP layouts for various housing sizes and pin numbers:
  - LQFP; PQFP; TQFP
  - Layer 1 24 to 144 pins, 0.50 mm pitch, sq.
  - Layer 2 24 to 144 pins, 0.65 mm pitch, sq.
- Component sides with solder resist mask
- Four pin rail rows 2 x 18 pole, basic grid 2.54 mm, borings 1.00 mm Ø
- size 57.2 x 57.2 mm