


QFP Multiadapter 240



RE472



- EPOXY resin FR4 1.50 mm double-sided 35 µm CU (pth)
- chem. NI/AU
- Two universal QFP layouts for various housing sizes and pin numbers:
 - LQFP; PQFP; TQFP
 - Layer 1 144 - 240 pins, 0.50 mm pitch, sq.
 - Layer 2 144 - 240 pins, 0.65 mm pitch, sq.
- Component sides with solder resist mask
- Four pin rail rows 4 x 15 pole, basic grid 2.54 mm, borings 0.90 mm Ø
- Size 70.00 x 70.00 mm