

## Product Spec Sheet

### Uno Charger UCK1

**Model Name:** Uno

**Description :** All Chemistry Fast Charger.

**Contents:** : Charger plate, AC Mains Adapter & Car Charging Cord, 4 assorted Adaptor plates.

(Optional Parts : Extra Adapter Plates )

**Input :** 12-24VDC, Min. 12W.

**Output :** Max. 950 mA.

**Discharge Current :** Approx. 200 mA.

**Charge Mode :** Negative Delta V for Ni-Cd/Ni-MH batteries.

Constant Current + Constant Voltage for Li-Ion and SLA batteries.

**Timer Control :** Max. 8.5 Hours.

**Charge Time :** Approx. 80 minutes for a 6V/1200 mAh Ni-Cd/Ni-MH battery.

**LED Indicator :** **Red** - Quick Charging / **Green** - Fully Charged / **Yellow** - Discharge

**Features :** 1. Made with Intelligent Microprocessor and Universal Circuitry to work with all 3.6V-12V Ni-Cd,

Ni-MH, Li-Ion & SLA batteries properly.

2. Featured with discharge capability to eliminate the memory effect of Ni-Cd/Ni-MH batteries.

3. Built with Over Voltage, Short Circuit Protection and Back-up Timer for total charge-safety.

4. With Yellow/Red/Green LED's to indicate discharge/charge/fully charged status precisely.

5. Featured with interchangeable adapter plates to fit virtually all Camcorder/Digital Camera batteries.

6. Flexible to use with Household AC or Car DC power source.



**Dimensions :** 140 mm (L) x 69 mm (W) x 25 mm (H)