

## HyperLink Wireless 14x12x7 Inch Weatherproof NEMA 4X Enclosure Model: NB141207

### Applications and Features

---

**Features:**

- Molded fiberglass reinforced polyester enclosure
- Stainless steel quick release latches with padlock hasps
- Fully gasketed raised lid
- Integral mounting flange
- NEMA Type 4, 4X / IP66 rated\*
- RoHS Compliant
- Optional universal equipment shelf and mounting brackets available
- Fully customized configurations available

**Applications:**

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments
- Hotspot applications
- Protection of equipment from theft or damage



### Product Description

---

The box is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded fiberglass reinforced polyester, it is well suited for high temperature or corrosive environments. The mounting flange allows it to be wall mounted as well as on a flat surface. The raised lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The raised lid is fully gasketed. The enclosure material is UV stabilized and comes in machine tool gray.

The NB141207 is ideal for custom applications, which may require special modifications to the enclosure. Mounting stand-offs inside the enclosure can be used for mounting plates. Blank mounting plates are available from Hyperlink.

**Specifications**

|                                 |   |
|---------------------------------|---|
| <b>Enclosure Material</b>       | Fiberglass Reinforced Polyester                     |
| <b>Enclosure Color</b>          | Machine Tool Gray                                   |
| <b>Weight</b>                   | 9.0 lbs (4.1 kg)                                    |
| <b>Outside Dimensions (max)</b> | 15.5 x 13.5 x 7.7 inches<br>(39.3 x 34.2 x 19.5 cm) |
| <b>Inside Dimensions</b>        | 13.5 x 11.5 x 5.8 inches<br>(34.3 x 29.2 x 14.7 cm) |
| <b>Flame Rating</b>             | UL 94-5V  |
| <b>RoHS Compliant</b>           | Yes   |
| <b>Ratings*</b>                 | NEMA Type 4, 4X / IP66                              |

\*Note: Enclosure ports (Cable conduit connector and N-type holes for lightning protectors or connectors) must be properly sealed to maintain NEMA type 4, 4X / IP66 rating.

**Enclosure Dimensions**

