



Ordering number C11773
Description C11773_Venla-S-Vega

Family	Venla	FWHM	13 degrees
Type	Reflector	Efficiency	-
LED	Luxeon S	cd/lm	-
Color	Metal	Gerber File	Available
Diameter	45 mm		
Height	25 mm		
Style	Round		
Optic Material	-		
Holder Material	PC		
Fastening	-		
Status	Ready		



Ordering number C11775
Description C11775_Venla-M-Vega

Family	Venla	FWHM	28 degrees
Type	Reflector	Efficiency	-
LED	Luxeon S	cd/lm	-
Color	Metal	Gerber File	Available
Diameter	45 mm		
Height	25 mm		
Style	Round		
Optic Material	-		
Holder Material	PC		
Fastening	-		
Status	Ready		



Ordering number C11776
Description C11776_Venla-W-Vega

Family	Venla	FWHM	48 degrees
Type	Reflector	Efficiency	-
LED	Luxeon S	cd/lm	-
Color	Metal	Gerber File	Available
Diameter	45 mm		
Height	25 mm		
Style	Round		
Optic Material	-		
Holder Material	PC		
Fastening	-		
Status	Ready		



Ordering number C11777
Description C11777_Venla-WW-Vega

Family	Venla	FWHM	56 degrees
Type	Reflector	Efficiency	-
LED	Luxeon S	cd/lm	-
Color	Metal	Gerber File	Available
Diameter	45 mm		
Height	25 mm		
Style	Round		
Optic Material	-		
Holder Material	PC		
Fastening	-		
Status	Ready		



Venla series



Venla series

Specially designed for Luxeon S series of LEDs.

Reflector material optical grade metal and protective lacquer coated PC (120 degrees of Celcius/24 degrees of Fahrenheit). Allows use of high current and temperature conditions.