




1

2

3

4

5



TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: NYLON 66
COLOR: GREY
PITCH: 1.50MM

ENVIRONMENTAL
OPERATING TEMPERATURE: -25 UP TO 85°C
FLAMABILITY RATING: UL94-V0
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 1A
WORKING VOLTAGE: 50V AC
INSULATOR RESISTANCE: >1000 MOHM
DIELECTRIC WITHSTANDING VOLTAGE: 500V AC/MN

PACKAGING
BAG

DIMENSION
A = 1.50 x (NB. PIN - 1)
B = 1.50 x (NB PIN) + 0.30
C = 1.50 x (NB PIN + 1) - 0.40

RoHS Compliant

G				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15	
F						
E						
D						
C	01-FEB-07	DRAW	EC	APPROVAL: RJ	UNIT: MM	DESCRIPTION: 1.50MM FEMALE TERMINAL HOUSING
B	31-MAR-04	LEAD FREE	JP		SCALE:	
A	04-SEP-98	PDF	JP		SHEET: 1/1	SIZE A4
REV	DATE	FILE	BY		DRAW: PEARL	

A

B

C

D