

CONFIGURATION		PART NUMBER
Female Receptacle, 8 Pin, 16 Awg, Shell 12		RT00128SNH
DIMENSIONS		
TECHNICAL DATA		
TEMPERATURE RANGE:	-40°C to + 105°C	
PROTECTION:	IP67 in mated condition and in combination with sealed backshell	
VOLTAGE RATING:	250V	
HOUSING BODY:	Zinc Alloy, Nickel Plated	
COUPLING NUT:	-	
INSERT:	Glass-filled Thermoplastic UL94-V0	
SEAL:	NBR	
CURRENT:	13A	
CONTACT SIZE:	16Awg	
APPROVALS:	UL ECBT2	