



Version Information	
Product Name	Microsoft® Wireless Desktop 2000
Product Version	Microsoft Wireless Desktop 2000
Keyboard Version	Microsoft Wireless Keyboard 2000
Mouse Version	Microsoft Wireless Mouse 2000
Transceiver Version	Microsoft 2.4 GHz Transceiver v7.0
Product Dimensions	
Keyboard Length	17.6 inches (447 millimeters)
Keyboard Width	7.29 inches (185 millimeters)
Keyboard Depth/Height	1.77 inches (45.1 millimeters)
Keyboard Weight	24.3 ounces (690 grams) includes 2 AAA alkaline batteries; typical battery weight may vary
Mouse Length	4.57 inches (116.1 millimeters)
Mouse Width	2.67 inches (67.9 millimeters)
Mouse Depth/Height	1.68 inches (42.7 millimeters)
Mouse Weight	4.94 ounces (140 grams) includes 2 AA alkaline batteries; typical battery weight may vary
Transceiver Length	1.83 inches (46.54 millimeters)
Transceiver Width	0.62 inches (15.75 millimeters)
Transceiver Depth/Height	0.31 inches (7.85 millimeters)
Transceiver Weight	0.18 ounces (5 grams)
Compatibility and Localization	
Interface	USB 2.0 Compatible
Operating Systems	<ul style="list-style-type: none"> • Microsoft Windows™ 7, Windows Vista®, and Windows XP (excluding Windows XP 64-bit) • Macintosh Mac OS X v10.4-10.6.X
Top-line System Requirements	<p>Requires a PC that meets the requirements for and has installed one of these operating systems:</p> <p>For Windows-based PC:</p> <ul style="list-style-type: none"> • Windows 7, Windows Vista, or Windows XP (excluding Windows XP 64-bit) • 100 MB Hard Drive Space • USB Port • CD Rom • Microsoft IntelliPoint v8.0 and Microsoft IntelliType Pro v8.0 <p>For Macintosh PC:</p> <ul style="list-style-type: none"> • Mac OS X v10.4-10.6.X • 30 MB Hard Drive Space • USB Port • CD Rom • Microsoft IntelliPoint v8.0 for Macintosh and Microsoft IntelliType Pro v8.0 for Macintosh
Compatibility Logos	<ul style="list-style-type: none"> • Compatible with Microsoft Windows 7 • Mac logo • Universal Mac logo • Certified USB logo
Software Localization	<p>For a Microsoft Windows-based PC:</p> <p>Microsoft IntelliPoint software and Microsoft IntelliType Pro software may be installed in Simplified Chinese, Traditional Chinese, English, French, German, Italian, Japanese, Korean, Brazilian Portuguese, Iberian Portuguese, or Spanish. If available, standard setup will install the software in the default OS language. Otherwise, the English language version will be installed.</p> <p>For a Macintosh PC:</p> <p>Microsoft IntelliPoint for Mac software and Microsoft IntelliType Pro for Mac software will install in English, French, German, Italian, Japanese, Brazilian Portuguese, and Spanish. User settings for OS language preference determine which localized version of the software is displayed. In the event that OS language preferences are not supported, the English language version will be displayed.</p>
Keyboard Localization	<p>Available language sets will vary by product and sales channel.</p> <p>104 key configuration: Arabic, Czech, English (Canada), English (North America), Greek, Hebrew, International English (Euro), International English (ROW), Russian, Simplified Chinese, Thai, and Traditional Chinese</p> <p>105 key configuration: All Nordic, English (UK), French (Belgium/Azerty), French (Canada), French (France), German (Germany), German (Switzerland/Luxemburg), Hungarian, Iberian (Portuguese), Italian, Spanish (Euro), Spanish (Latin America), and Turkish</p> <p>106 key configuration: Korean</p> <p>107 key configuration: Brazilian</p> <p>109 key configuration: Japanese</p>
Tracking Technology	
Mouse Tracking System	Microsoft-proprietary BlueTrack™ Technology
Imaging Rate	Dynamically adaptable to 8000 frames per second
X-Y Resolution	1000 points per inch (39.4 points per millimeter)
Tracking Speed	Up to 72 inches (1829 millimeters) per second
Wireless Technology	
Wireless Frequency	2.4 GHz frequency range
Wireless Range	Up to 30 feet (10 meters) typical. Note: RF range is affected by many factors, such as nearby metallic objects and relative positioning of the mouse and receiver.
Product Feature Performance	
QWERTY Key Life	5,000,000 actuations per key
Hot Key Features	My Favorites, My Favorites 1, My Favorites 2, My Favorites 3, My Favorites 4, My Favorites 5, Web/home, Mail, and Calculator
Hot Key Life	1,00,000 actuations per key
Media Key Features	Mute, Volume +, Volume -, Next Track, Previous Track, Zoom +, Zoom -, and Play/Pause
Media Key Life	1,00,000 actuations per key
Typing Speed	1000 characters per minute
Mouse Button Features	3 buttons including scroll wheel button
Right & Left Button Life	3,000,000 actuations at no more than 4 actuations per second
Wheel Button Life	350,000 actuations at no more than 4 actuations per second
Mouse Scrolling Features	Tilt wheel enables vertical and horizontal scrolling
Wheel Vertical Scrolling Life	<ul style="list-style-type: none"> • 100,000 revolutions (away from user) • 300,000 revolutions (towards user)
Storage Temperature & Humidity	-40 °F (-40 °C) to 140 °F (60 °C) at < 5% to 65% relative humidity (non-condensing)
Operating Temperature & Humidity	32 °F (0 °C) to 104 °F (40 °C) at < 5% to 80% relative humidity (non-condensing)
Power Requirements	
Battery Type and Quantity	<ul style="list-style-type: none"> • Keyboard: 2 AAA alkaline batteries (included) • Mouse: : 2 AA alkaline batteries (included)
Battery Life	<ul style="list-style-type: none"> • Keyboard: 18 months typical • Mouse: Up to 8 months typical

Certification Information	
Country of Manufacture	People's Republic of China (PRC)
ISO 9001 Qualified Manufacturer	Yes
ISO 14001 Qualified Manufacturer	Yes
Restriction on Hazardous Substances	This device complies with all applicable worldwide regulations and restrictions including, but not limited to: EU directive 2002/95/EC on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment and EU Registration Evaluation and Authorization of Chemicals (REACH) regulation regarding Substances of Very High Concern.
FCC/IC ID	This Class B digital apparatus complies with Part 15 of the U.S. Federal Communications Commission (FCC) rules, Canadian ICES-003, and RSS-210. Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Tested to comply with FCC (U.S. Federal Communications Commission) Standards. For home or office use. The term "IC:" before the certification/registration number only signifies that the Industry Canada technical specifications were met. Model numbers: 1477, Wireless Keyboard 2000; 1416, Wireless Mobile Mouse 2000 and 1423, Microsoft 2.4GHz Transceiver v7.0. FCC IDs: C3K1477, C3K1416, and C3K1423. IC IDs: 3048A-1477, 3048A-1416, and 3048A-1423.
Agency and Regulatory Marks	<ul style="list-style-type: none"> • ACAMED Declaration of Conformity (Australia and New Zealand) • ANATEL Certificate (Brazil) • IC ID, Certificate of Acceptance (Canada) • SUBTEL Certificate (Chile) • CMIIT Certificate (China) • EIP Pollution Control Mark, EPUP (China) • NTRA Certificate (Egypt) • R&TTE Declaration of Conformity, Safety and EMC (European Union) • WEEE (European Union) • ETA Certificate (India) • POSTEL Certificate (Indonesia) • VCCI and TELEC Certificates (Japan) • KC Certificate (Korea) • SIRIM Certificate (Malaysia) • NTC Certificate (Philippines) • FAC and GOST Certificates (Russia) • IDA Registration (Singapore) • BSMI and NCC Certificates (Taiwan) • SDoC Certificate (Thailand) • TRA Certificate (United Arab Emirates) • FCC ID, Grant of Equipment Authorization (USA) • UL and cUL Listed Accessory (USA and Canada) • CB Scheme Certificate (International)
Windows Hardware Quality Labs (WHQL)	Desktop ID: 1444501 Microsoft Windows 7

Results stated herein are based on internal Microsoft testing. Individual results and performance may vary. Any device images shown are not actual size. This document is provided for informational purposes only and is subject to change without notice. Microsoft makes no warranty, express or implied, with this document or the information contained herein. Review any public use or publications of any data herein with your local legal counsel.

©2011 Microsoft Corporation. The names of actual companies and products mentioned herein may be trademarks of their respective owners.