
Item no.: 2001-1407
Product description: 4-CONDUCTOR GROUND TERMINAL BLOCK SUITABLE FOR EX E APPLICATIONS



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [AWG]	22 - 14 AWG
Connection method	CONTACT CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.25 - 2.5 mm ²
Cross section [AWG]	22 - 14 AWG
Wiring method	e+f
Connection method	CONTACT CAGE CLAMP® CONNECTION
Weight	8.4 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	33 mm
Height	1.299 in
Width	4.2 mm
Width	0.165 in
Depth	70 mm
Depth	2.76 in
Strip length from	9 mm

Strip length to
Strip length

11 mm
0.39 in



Country of Origin
Customs Tariff No.
Mounting

Deutschland
85369010
TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
2001-1407	ABS	05-HG476175/1-PDA			0,5-2,5
2001-1407	AEX	E185892			22-14
2001-1407	CCA	NL6386			0,5-1,5/2,5
2001-1407	CSA	154112-1645434			22-14
2001-1407	GL	26187-05HH			0,25-1,5
2001-1407	IECEX	IECEXPTB03.0004U			0,5-2,5
2001-1407	KEMA	2116586.01			0,5-2,5
2001-1407	LR	91/20112(E6)			0,25 -2,5
2001-1407	PRS	TE/1718/880590/08			0,5-2,5
2001-1407	PTB	PTB05Atex1094U			0,5-2,5
2001-1407	RosTest	8189158			0,5-2,5
2001-1407	UR	E45172			22-14

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected