

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212010001](#)
Status: **Active**
Overview: [mpm_connectors](#)
Description: mPm® DIN Valve Connector, Type A, 2 Pole, Terminal No Tails, Black, Nitrile Gasket with IP67 Screw

Documents:

Drawing (PDF)	Test Summary STR-1251 (PDF)
Product Specification PS-121201-001 (PDF)	Test Summary TS-121201-001 (PDF)
Packaging Specification PK-121201-001 (PDF)	RoHS Certificate of Compliance (PDF)



image - Reference only

General

Product Family	Field Attachable / Accessories
Series	121201
IP Rating	IP67
Overview	mpm_connectors
Product Name	mPm®
Type	Field Attachable Connector

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Orientation	90° Angle
Poles	2
Temperature Range - Operating	-25°C to +75°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16A
Voltage - Maximum	250V AC/DC

Material Info

Old Part Number	C28200N0R
-----------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-121201-001
Product Specification	PS-121201-001
Sales Drawing	SD-121201-002
Test Summary	STR-1251, TS-121201-001

EU RoHS

RoHS Compliant by Exemption
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[121201Series](#)